


Guía para Solicitud: liners Alpha TrūSeal



PERFIL SIMÉTRICO AK



- 9 mm de espesor distalmente para la máxima comodidad.
- Giratorio para extender la vida del liner

TABLA DE TAMAÑOS DEL LINER ALPHA TRŪSEAL

Cónico

	25	26.5	28	30	32	34	37	40	43
Proximal Measurement	37 - 49 cm (14.5 - 19.25 in)	39 - 51 cm (15.25 - 20 in)	40 - 54 cm (15.5 - 21.25 in)	42 - 58 cm (16.5 - 23 in)	44 - 62 cm (17.25 - 24.5 in)	46 - 66 cm (18 - 26 in)	49 - 72 cm (19.25 - 28.25 in)	52 - 78 cm (20.5 - 30.75 in)	55 - 85 cm (21.5 - 33.5 in)
Distal Measurement	25 - 26.5 cm (9.75 - 10.5 in)	26.5 - 28 cm (10.5 - 11 in)	28 - 30 cm (11 - 11.75 in)	30 - 32 cm (11.75 - 12.5 in)	32 - 34 cm (12.5 - 13.5 in)	34 - 37 cm (13.5 - 14.5 in)	37 - 40 cm (14.5 - 15.75 in)	40 - 43 cm (15.75 - 17 in)	43 - 47 cm (17 - 18.5 in)

Size	Part #
25	S494-1125
26.5	S494-1126
28	S494-1128
30	S494-1130
32	S494-1132
34	S494-1134
37	S494-1137
40	S494-1140
43	S494-1143

Optional

ALA-VM-S2

Alpha Silicone
Volume Management
Pads, set of 2

Cilíndrico

	32	34	37	40	43	47
Proximal Measurement	39 - 44 cm (15.25 - 17.25 in)	41 - 47 cm (16 - 18.5 in)	44 - 53 cm (17.25 - 20.75 in)	47 - 59 cm (18.5 - 23.25 in)	50 - 65 cm (19.5 - 25.5 in)	54 - 74 cm (21.25 - 29.25 in)
Distal Measurement	32 - 34 cm (12.5 - 13.5 in)	34 - 37 cm (13.5 - 14.5 in)	37 - 40 cm (14.5 - 15.75 in)	40 - 43 cm (15.75 - 17 in)	43 - 47 cm (17 - 18.5 in)	47 - 51 cm (18.5 - 20 in)

Size	Part #
32	S495-1132
34	S495-1134
37	S495-1137
40	S495-1140
43	S495-1143
47	S495-1147

Optional

ALA-VM-S2

Alpha Silicone
Volume Management
Pads, set of 2